


249.SR - Non sparking drift punches



Description:

- Special non sparking and anti-magnetic Copper-Beryllium alloy.

|  | A [mm] | Diameter [mm] | Length L [mm] | Length L1 [mm] | Weight [g] |
|--|--------|---------------|---------------|----------------|------------|
| 249.10SR | 10.0 | 16.0 | 145.0 | 45.0 | 200.0 |
| 249.12SR | 12.0 | 18.0 | 160.0 | 50.0 | 280.0 |
| 249.3SR | 3.0 | 9.0 | 110.0 | 20.0 | 20.0 |
| 249.4SR | 4.0 | 10.0 | 110.0 | 35.0 | 60.0 |
| 249.6SR | 6.0 | 12.0 | 115.0 | 35.0 | 105.0 |
| 249.8SR | 8.0 | 14.0 | 120.0 | 40.0 | 130.0 |