



Chemical protection

TELSOL 351

Frequent contact | continuous wear

Comfort, flexibility and mechanical protection with low risk of chemical hazards

SPECIFIC ADVANTAGES



Thermal protection

- Exceptional comfort and good resistance to cold, due to the seamless cotton-knit



Durability

- Good resistance to oils, greases and hydrocarbons



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Mechanical industry
- Other industries

APPLICATIONS

- Maintenance in wet environments (water, oil, greases, hydrocarbons)
- Maintenance in wet environments
- Pharmaceutical industry: maintenance and cleaning



CHEMICAL PROTECTION
TYPE A

EN388



4121X

EN ISO 374-1



TYPE A
KLMNPT

EN ISO 374-5



CATEGORY 3

DEXTERITY



0334

EN ISO 21420:
5/5



Chemical protection

TELSOL 351

Frequent contact | continuous wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
4 1 2 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	K: Sodium hydroxide 40%
	L: Sulphuric acid 96%
	M: Nitric acid 65%
	N: Acetic acid 99%
	P: Hydrogen peroxide 30%
	T: Formaldehyde 37%
TYPE A	
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Textile support
Exterior finish	Pebbled
Material	PVC
Cuff characteristic	Feston Cuff
Colour.s	Blue
Length (cm)	30
Thickness (mm)	1.35
European sizes	8 9 10
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	1.1E+9 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	1.8E+9 Ω

LOGISTIC DETAILS

Packaging	12 pairs/bag 72 pairs/carton
-----------	---------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/10/18/2082
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France