

Metric Size - TU TU0425P1-20

Datasheet

- Applicable tubing O.D.: Ø 2 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- 29 colour variations.

Standard specifications

Size	0425 (O.D. Ø4 I.D. Ø2.5)
Color	P1 (Neon Pink)
Roll Length	20 m
Reel Length	None
Suffix	None
-	Air, Water
Max. operating pressure at 20 °C	0.8 MPa

Additional information

Catalogue

[TU-29COLOR-A_EU.pdf](#)