

# Product datasheet

Specifications



## Thorsman Glands - cable gland - grey - M40 - diameter 19 to 28

Local distributor code:

398239392

ISM71506

EAN Code: 3606480077234

### Main

product range	Thorsman Glands
product type	Cable gland
colour	Grey (RAL 7035)
quantity per package	Set of 5

### Complementary

Material	PA6
ISO thread	M40
Cable outer diameter	19...28 mm

### Environment

IP-Class	IP68
operating temperature	-30...80 °C permanently -30...150 °C intermittently

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.000 cm
Package 1 Width	16.000 cm
Package 1 Length	1.000 cm
Package 1 Weight	50.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	24.000 cm
Package 2 Width	16.000 cm
Package 2 Length	5.000 cm
Package 2 Weight	275.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	30.000 cm
Package 3 Width	37.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Package 3 Length	56.000 cm
Package 3 Weight	12.240 kg

### Logistical informations

Country of origin	TR
-------------------	----

### Contractual warranty

Warranty	18 months
----------	-----------





## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

<b>Materials and Substances</b>	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	<a href="#">REACH Declaration</a>

### Use Again

<b>Repack and remanufacture</b>	
Take-back	No