

## Office mouse, wireless

00173022 "MW-300 V2" Optical 3-Button Wireless Mouse, Quiet, USB Receiver, red



### Highlightstext:

- Compact, optical wireless mouse with nano receiver for super-precise and soft mouse pointer control
- Noiseless main buttons for relaxed working without disturbing noise
- Storable USB receiver can be transported inside the mouse to save space
- The ultra-small USB receiver is suitable for permanent installation in a notebook or PC
- Reliable 2.4 GHz wireless technology with a range of 10 metres (depending on use and environmental conditions)
- Smart-Link technology for easy start-up
- The silent computer mouse does not make any clicking noises
- Polymer-coated gliding feet ensure fluid mouse movements and uninterrupted working
- Suitable for left- and right-handed users
- Rubber scroll wheel included

### System Requirements:

- Operating system: Windows 11/10/8/7, MacOS 10.10 or later

### Technical characteristics:


- Colour: Black/Red
- Form factor: Right and left handed
- Shade of colour: Red
- Connection: USB-Typ-A-Plug
- Connection: 2.4 GHz RF
- Battery life (depending on usage): 60 d
- Compatible operating systems: MAC OS 10.10 or higher/Windows 11/10/8/7
- DPI-Range: 1200
- Max. DPI: 1200
- Range: 10 m
- Special features: Power saving mode/Rubberised surface
- Model: Standard Mouse
- Mouse - Keys: Whisper
- Mouse wheel (material): Gummiert
- Number of Mouse Buttons: 3 Buttons incl. Scroll Wheel
- Sensors: Optical
- Width x Height x Depth: 5.8 x 3.7 x 10.3 cm
- Battery Type: AAA Micro
- Number of Batteries: 2

### Delivery:

- 1 "MW-300 V2" optical wireless mouse
- 1 USB receiver
- 2 AAA Micro batteries
- 1 operating manual

## Office mouse, wireless

00173022 "MW-300 V2" Optical 3-Button Wireless Mouse, Quiet, USB Receiver, red

 4 047443 479716	Brand	Item-no.	VE	MB	Quanti
	<i><b>hama</b></i>	00173022	6	1	1