

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202480004](#)
Status: **Active**
Overview: [Brad Passive-Signal and Safety MPIS Boxes](#)
Description: MPIS Micro-Change (M12) Passive Junction Box, Top Mount, 4 Ports, LED for PNP Sensor, WSOR Cable, 5.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Passive Distribution Boxes
 Series [120248](#)
 IP Rating IP67
 Overview [Brad Passive-Signal and Safety MPIS Boxes](#)
 Product Name MPIS
 UPC 889056140768

Physical

Bus I/O N/A
 Cable Connector Orientation Straight
 Cable Length 5.0m
 Home Run Cable Length 5.0m
 Home Run Connector N/A
 Home Run Interface Pigtail
 Keyway A-coded
 LED Indicator PNP Sensors
 Material - Cable Jacket TPU
 Material - Housing PBT
 Material - Metal Copper Alloy
 Material - Plating Mating Gold over Nickel
 Net Weight 621.257/g
 Orientation Top Mount
 Poles 4
 Poles (wired) 4
 Ports 4
 Temperature Range - Operating -25°C to +85°C
 Wire/Cable Type WSOR
 Wiring Configuration Single I/O per Port

Electrical


Current - Maximum per Contact 12.0A per module, 4.0A per port
 Functional Wiring PNP
 Voltage - Maximum 10-30V DC

Material Info

Engineering Number BTB400P-FBW-05

Reference - Drawing Numbers

Sales Drawing 1202480001-000



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120248 Series](#)