
Product data sheet





Cordless Drill/Driver

GSR 18V-28



Professional performer in the 18 V category

The most important data

Torque (soft/hard/max.)	28/63/- Nm
No-load speed (1st gear / 2nd gear)	0 - 500 / 0 - 1,900 rpm
Max. screw diameter	8 mm

Part Number 0 601 9H4 100

> More product information

Technical data

Technical data

Torque (soft/hard/max.)	28/63/- Nm
No-load speed (1st gear / 2nd gear)	0 - 500 / 0 - 1,900 rpm
Battery type	Lithium-lon
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18.0 V
Weight excl. battery	1.2 kg
Torque settings	20+1
Packaging dimensions (width x length x height)	269 x 321 x 111 mm
Drilling diameter	
Max. drilling diameter in wood	38 mm
Max. drilling diameter in steel	13 mm
Screw diameter	
Max. screw diameter	8 mm

Noise/vibration information

Drilling in metal

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- 63 Nm of hard torque ensures professional performance
- 13-mm full-metal chuck makes it highly durable, ensuring less wear and longer use
- Compact ergonomic design enables comfortable handling for convenient work





