



AMP

TE Internal #: 539755-2
Portable Crimp Tools, Commercial Crimp Tooling, Operator
Releasable & Adjustable, Removable/Interchangeable, TE Product
Specification (114-), Manual
[View on TE.com >](#)

Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed





Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 963922-1 BUTT SPLICE LP 1.0-2.5 MM2 PTP CUSN4	 TE Part # 963920-1 BUTT SPLICE LP 0.2-0.5 MM2 PTP CUSN4	 TE Part # 1-962889-1 LOCKING TAB REC	 TE Part # 963921-1 STOSSVERBINDER
 TE Part # 1-962890-1 TAB RECEPTACLE 0.5-1.0 MM2 PTPPHBZ	 TE Part # 1-962891-1 FAST STECKHUELSE3,3	 TE Part # 2-962889-1 NO DESCRIPTION	 TE Part # 3-962889-1 NO DESCRIPTION

Customers Also Bought

 TE Part #DT04-2P DEUTSCH DT HOUSINGS	 TE Part #W2S DEUTSCH DT WEDGELOCKS	 TE Part #282104-1 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	 TE Part #206070-8 CABLE CLAMP KIT #17
---	---	---	--



Documents

Product Drawings

ERGOCRIMP DIE SET,INCL LOCATOR, LOCK.TAB

English

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

German