USB/Micro USB










Range Overview

△ Receptacle to Overmolded with Cable




△ Receptacle with Cable to Overmolded with Cable







□ Accessories




Specification | USB Type A/B

Identifications	USB Type A 3.0 USB Type A 2.0 USB Type B 2.0 Mini USB Type B 2.0
Description	Receptacle Receptacle With Cable Overmolded with Cable Field Installable
Current Rating / Data	USB 2.0: 1.5A USB 3.0: 1A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing): PBT, UL94V-0
Waterproof Rating	IP67/68
	Receptacle: Nylon+GF: -40°C~105°C M-PPE: -40°C~105°C ABS: -20°C~80°C
Temperature Range	Receptacle with cable: Nylon+GF: -20°C~105°C ABS: -20°C~80°C Overmolded with Cable: -20°C~80°C Field Installable: -20°C~80°C
Temperature Range Contact Resistance	Receptacle with cable: Nylon+GF: -20°C~105°C ABS: -20°C~80°C Overmolded with Cable: -20°C~80°C
	Receptacle with cable: Nylon+GF: -20°C~105°C ABS: -20°C~80°C Overmolded with Cable: -20°C~80°C Field Installable: -20°C~80°C

Specification | USB Type C

Identifications	USB Type C 3.1
Description	Receptacle Overmolded with Cable
Current Rating / Data	3A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing): PP, UL94V-0, f1 Rated
Waterproof Rating	IP68
Temperature Range	-40°C ~105°C
Contact Resistance	-40°C ~105°C ≤ 50mΩ


Ordering Information | USB & Mini USB



e.g.(01) = 1M

Ordering Information | USB | Double-ended

ALTW waterproof connector to ALTW waterproof connector ALTW waterproof connector to Standard USB connector (None Waterproof)



Physical Dimension | USB

∠ Receptacle

Panel Cut-Out



Type C




Ту	/pe	Mating Style	Housing Gender	L	OD
	Type A	Screw Thread		19.4	20.8
USB2.0	туре А	2 Points Lock Bayonet		19.4	20.8
U3B2.U	T D	Screw Thread		19.4	20.8
	Туре В	2 Points Lock Bayonet	Male	23.6	25.6
USB3.0	Tuno A	Screw Thread		19.4	20.8
0303.0	Туре А	2 Points Lock Bayonet		23.6	25.6
Mini USB	i USB - Screw Thread			14.8	15.6
USB3.1	Туре С	Quick	Female	16.7	11.3

^{*} Maximum Panel Thickness: USB: 4mm I Mini USB: 2.5mm

Unit: mm

Connector Dimension




Ш		
ab	le	

Ту	Type Mating Style		Housing Gender	W(A)	W(B)	W(C)	L1	L2						
		Screw Thread		19.0	25.4	29.3	22.0	-						
USB2.0	Type A	2 Points Lock Bayonet		23.2	28.5	32.9	20.3	-						
0302.0		Screw Thread		19.0	25.4	29.3	22.0	-						
	Type B	2 Points Lock Bayonet	Male	23.2	28.5	32.9	20.3	-						
		Screw Thread		19.0	25.4	29.3	-	37.2						
USB3.0	Type A	2 Points Lock Bayonet		23.2	28.5	32.9	-	37.5						
Mini USB	-	Screw Thread		14.5	20.6	23.5	15.0	-						
* USB: S	crew I M	liddle Size (13/16	"-28 UNS)				* USB: Screw Middle Size (13/16"-28 UNS) Unit: mm							

* USB: Screw I Middle Size (13/16"-28 UNS)

2 Points Lock Bayonet I Large Size (1"20 UNEF)

^{*}Mini USB: Screw I Standard Size (5/8"-27 UNS)






Ту	pe	Mating Style	Housing Gender	W(A)	W(B)	W(C)	W(D)	L1
USB3.1	Type C	Quick	Female	10.8	14.2	19.6	25.1	21.0

^{*}Recommended Screw Size: M2x0.4x10mmL (min.)

Unit: mm

Receptacle | Overmolded with Cable | Field Installable

∠ Overmolded with Cable




Ту	rpe	Mating Style	Housing Gender	L	OD
		Screw Thread	Female	42.6	25.4
	Type A	Screw Illieau	Male	45.0	20.6
	Туре А	2 Points Lock Bayonet	Female	73.3	28.5
USB2.0		2 Folints Lock Dayonet	Male	-	-
0302.0		Screw Thread	Female	42.6	25.4
	Type B	Screw Illieau	Male	45.0	20.6
	Туре в	2 Dainta Lask Bayenst	Female	73.3	28.5
		2 Points Lock Bayonet	Male	-	-
		Screw Thread	Female	42.6	42.6
USB3.0	Type A	Screw Illieau	Male	45.0	20.6
0383.0	Type A	2 Points Lock Bayonet	Female	75.0	28.5
		2 Folints Lock Bayonet	Male	-	-

^{*} USB: Screw I Middle Size (13/16"-28 UNS)

Unit: mm

^{*}Mini USB: Screw I Standard Size (5/8"-27 UNS)




Туре		Mating Style	Housing Gender	L(A)	L(B)	OD
	Type A	Screw Thread		=	=	=
USB2.0	туре А	2 Points Lock Bayonet		46.8	44.1	28.5
0302.0	Typo B	Screw Thread	Female	=	=	=
	Type B	2 Points Lock Bayonet		46.8	44.1	28.5
USB3.0	Type A	Screw Thread		-	-	-
USB3.0 Type A		2 Points Lock Bayonet		-	-	-
Mini USB	-	Screw Thread		-	1	1

^{*} USB: Screw I Middle Size (13/16"-28 UNS) 2 Points Lock Bayonet I Large Size (1"20 UNEF)

Unit: mm


² Points Lock Bayonet I Large Size (1"20 UNEF)

USB Type A/B/C | Mini USB Type B Receptacle | Overmolded with Cable | Field Installable



Ту	pe	Mating Style	Housing Gender	W	L
USB2.0/3.0	Type C	Quick Lock	Male	14.2	51.1

Unit: mm



Ту	pe	Mating Style	Mating Style Housing Gender		OD
	Tuno A	Screw Thread		56.0	20.6
USB2.0	Type A	2 Points Lock Bayonet		-	-
USB2.0	T D	Screw Thread	Screw Thread	56.0	20.6
	Type B 2 Points Lock Bayonet Male		Male	-	-
USB3.0	Tuno A	Screw Thread		-	-
USB3.0 Type A		2 Points Lock Bayonet		-	-
Mini USB	-	Screw Thread		45.0	15.45


* USB: Screw I Middle Size (13/16"-28 UNS)

2 Points Lock Bayonet I Large Size (1"20 UNEF)


^{*}Mini USB: Screw I Standard Size (5/8"-27 UNS)

Product Features | USB


∠ Receptacle










○ Overmolded with Cable







✓ Field Installable








Find Our Standard Products | USB

□ USB > In-line

Middle Size



USB > In-line

Male Connector	Field Installable	Overmolded with Cable	Overmolded with Cable (Double-Ended)
(Housing) • Female Contacts • Screw Thread • Middle Size (13/16"-28 UNS)		*** USB 2.0: Choose the cable length from 01~05m	Non-Waterproof *** USB 2.0: Choose the cable length from 01~05m
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB Type A 2.0	UA-20BMFA-SL8001	UA-20BFMM-SL7A <u>XX</u> **	UA-20BFM-SA7A <u>XX</u> ** UA-20BFM-SB7A <u>XX</u> **
USB Type B 2.0	UB-20BMFA-SL8001	UB-20BFMM-SL7A <u>XX</u> **	UB-20BFM-SA7A <u>XX</u> ** UB-20BFM-SB7A <u>XX</u> **

USB/Micro USB I Find Our Standard Products

USB Type A | Type B

In-line | Receptacle and Mating Pair Screw Thread Middle Size

□ USB > In-line

Male Connector (Housing)	Overmolded with Cable> (Double-Ended)	Overmolded with Cable (Double-Ended)	Field Installable	
• Female Contacts • Screw Thread • Middle Size (13/16"-28 UNS)	USB2.0 and USB3.0	USB2.0 and USB3.0		
	** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m	** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m		
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)	
USB Type A 2.0	UA-20AMF-SA7A <u>XX</u> ** UA-20AMF-SB7A <u>XX</u> **	UA-20BFM-SA7A <u>XX</u> ** UA-20BFM-SA7A <u>XX</u> **	-	
USB Type A 3.0	UA-30AMF-SD7B <u>XX</u> **	UA-30BFM-SD7B <u>XX</u> **	-	
USB Type B 2.0	UB-20AMFM-SA7A <u>XX</u> ** UB-20AMFM-SB7A <u>XX</u> **	UB-20BFM-SA7A <u>XX</u> ** UB-20BFM-SB7A <u>XX</u> **	-	

Male Connector	Receptacle	Overmolded with Cable	Overmolded with Cable (Double-Ended)
(Housing) • Female Contacts • Screw Thread • Middle Size (13/16"-28 UNS)	Type 1 Type 2	** Choose the cable length from 01~05m	Non-Waterproof ** Choose the cable length from 01~05m
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB Type A 2.0	UA-20PMFP-SC8001 UA-20PMFP-SC8002 Type1 UA-20PMFP-SC8003 Type2	UA-20BFMM-SL7A <u>XX</u> **	UA-20BFM-SA7A <u>XX</u> ** UA-20BFM-SB7A <u>XX</u> **
USB Type B 2.0	UB-20PMFP-SC8001 UB-20PMFP-SC8002 UB-20PMFP-SC8003	UB-20BFMM-SL7A <u>XX</u> **	UB-20BFM-SA7A <u>XX</u> ** UB-20BFM-SB7A <u>XX</u> **

Receptacle and Mating Pair 2 Points Lock Bayonet Large Size

Male Connector	Receptacle	Overmolded with Cable	Field Installable
(Housing)	_IR7m		i loid motandole
• Female Contacts			
• 2 Points Lock Bayonet	u(\ ()=,		
(Nut OD: 28.5mm)			
• Large Size (1"20 UNEF)			
	Type 1 Type 2	** Choose the cable length from 01~05m	
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB Type A 2.0	UA-20PMFP-LC7001 UA-20PMFP-LC7002 Type1 UA-20PMFP-LC7003 Type2	UA-20AFMM-LL7A <u>XX</u> ** UA-20AFMM-LR7A <u>XX</u> **	-
USB Type B 2.0	UB-20PMFP-LC7001 UB-20PMFP-LC7002 UB-20PMFP-LC7003	UB-20AFMM-LL7A <u>XX</u> ** UB-20AFMM-LR7A <u>XX</u> **	-

riangle USB > Receptacle and Mating Pair

_ 055 11000P10010 0110 111011118 1 011			
Male Connector	Receptacle>	Overmolded with Cable	Field Installable
(Housing)			i i icia mistanabie
Female Contacts		=	
• 2 Points Lock Bayonet (Nut OD: 25.4mm)			
• Large Size (13/16-28 UN)			
		** Choose the cable length from 01~05m	
Speed	Male Connector (M)	Female Connector (F)	Female Connector (F)
Speed	Female Contacts (F)	Male Contacts (M)	Male Contacts (M)
USB Type A 2.0	UA-20PMFJ-NC7001	UA-20BFMM-NL7A <u>XX</u> **	-

Receptacle and Mating Pair | Receptacle with Cable and Mating Pair | 2 Points Lock Bayonet | Quick Lock Large Size

Male Connector (Housing) Female Contacts Screw Thread	Receptacle with Cable> (Double-Ended)	·····>	Overmolded with Cable (Double-Ended)
• 2 Points Lock Bayonet (Nut OD: 28.5mm) • Large Size (1"20 UNEF)	Non-Waterproof * USB 3.0: Choose the cable length from 150~300mm	** USB 3.0: Choose the cable length from 01~03m	*** USB 3.0: Choose the cable length from 01~03m
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB Type A 3.0	UA-30PMF-LD7B <u>XX</u> * UA-30PMF-SD7B <u>XX</u> *	UA-30AFMM-LL7B <u>XX</u> ** UA-30BFMM-SL7B <u>XX</u> **	UA-30BFM-SD7B <u>XX</u> ** UA-30AFM-LD7B <u>XX</u> **

□ USB > Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Quick Lock • Speed of Jack: USB Type C 3.1	Receptacle	Overmolded with Cable (Double-Ended) Ist End Choose the data transfer rate (G1) 3.1 Gen 1 or (G2) 3.1 Gen 2 XX: Choose the cable length from 01~03m	Field Installable
Speed of Plug	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
1st End: USB Type C 3.1 Gen 1/Gen 2 2nd End: USB Type C 3.1 Gen 1/Gen 2	UC-31PFFP-QS8001 UC-31PFFH-QF7001	UC- 2 AMM-QE8C <u>XX</u> * UC- 2 AMM-QF8C <u>XX</u> *	-
1st End: USB Type C 2.0 2nd End: USB Type A 2.0	-	UC-20AMM-QA8A <u>XX</u> *	-
1st End: USB Type C 3.0 2nd End: USB Type B 2.0	-	UC-30AMM-QD8B <u>XX</u> *	-

In-line Screw Thread Standard Size

→ Mini USB > In-line


Male Connector (Housing) Female Contacts Screw Thread Standard Size (5/8"-27 UNS)	Overmolded with Cable>	Overmolded with Cable	Field Installable
	** Choose the cable length from 01~04m	** Choose the cable length from 01~04m	
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
Mini USB Type B 2.0	NUB-20AMFM-SL7A <u>XX</u> **	NUB-20AFMM-SL7A <u>XX</u> **	-

→ Mini USB > In-line


Male Connector	Field Installable	Overmolded with Cable	Field Installable
(Housing)		ŕ	Tield ilistaliable
• Female Contacts			
• Screw Thread	ALTW ALTW		
• Standard Size (5/8"-27 UNS)			
		** Choose the cable length from 01~04m	
Speed	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
Mini USB Type B 2.0	NUB-20BMFA-SL7001	NUB-20AFMM-SL7A <u>XX</u> **	-


USB/Micro USB | Find Our Standard Products Mini USB Type B

Receptacle and Mating Pair Screw Thread Standard Size



Accessories






Specification | Micro USB


Identifications	Micro USB: AB Type
Description	Receptacle
Current Rating	1pin & 5pin: 1.8A 2pin, 3pin & 4pin: 1A
Materials	Contacts: Copper Alloy, Gold Plated Connector Body (Housing): Nylon, Black Shell: Stainless, Gold Plated Inner Gascket: Silicone, Transparent Outside Gasket: Silicone, Transparent
Waterproof Rating	IP67/68
Temperature Range	-30°C ~ 85°C
Contact Resistance	≤30mΩ
Insulatuib Resistance	≥ 1000MΩ at 100Vdc
Durability	10,000 Cycles
More to Know	SMT Temperature & Time: 260°C/5Sec

Ordering Information | Micro USB



Without Cable: Different Versions

Physical Dimension | Micro USB



Unit: mm

Find Our Standard Products | Micro USB

