

PRODUCT-DETAILS

# GRNY-100-9-C

## GROMMETING EXTD .10IN NAT NYL 100FT



### General Information

Extended Product Type	GRNY-100-9-C
Product ID	7TAG009750R0028
EAN	5414363023616
Catalog Description	GROMMETING EXTD .10IN NAT NYL 100FT
Long Description	Extruded Grommeting, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 5.58mm (0.220 Inch), Width of 5.33mm (0.21 Inch), Thickness 1.14mm (0.045 Inch), Width Maximum Panel Thickness of 2.54mm (0.1 Inch), 30.48m (100 Foot) Reel

### Ordering

EAN	5414363023616
UPC	728494119229

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	12 in 305 mm
Package Level 1 Height	1.75 in 44 mm
Package Level 1 Depth / Length	17 in 432 mm
Package Level 2 Units	10 piece
Package Level 2 Width	12.5 in

	318 mm
Package Level 2 Height	12 in
	305 mm
Package Level 2 Depth / Length	18 in
	457 mm

### Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Panel Thickness	0.1 in 2.54 mm
Product Name	NYLON GROMMETING
Product Type	Grommeting
Special Functions	Used to line panel edges and knockouts where the chafing of wires is a concern.

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GRNY-100-9-C
Instructions and Manuals	GRNY-100-9-C

### Classifications

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
UNSPSC	39131603
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5393 >> Grommet edging

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

