

Datasheet

RS Pro 24V, 2A Lead Acid Battery Charger, UK Plug

RS Stock No: **549-300**



Product Details

RS Pro lead acid battery charger is a high quality range of automatic charger with 3 stage controls. The charger yields 24 V output voltage at 2 A charge current. The UK plug type charger has a charging current(s) of 2 to 25 A with many models provided in aluminium impact resistant casing and supplied with UK and EU mains leads and crocodile clip connectors. The battery charger meets RoHS and CE directive standards.

Features and Benefits

- 3 stage control (fast/normal/float)
- Full charge with automatic shutdown
- Short circuit output protected
- Most models with 115/230 V input range
- Reverse polarity protected
- Overload protected
- UK/EU plugs
- LED indicator included
- Compliant to safety standards
- RoHS and CE directive compliant



ENGLISH

Specifications:

Battery Type Charged	Lead Acid
Number of Charge Stages	3
Plug Type	UK
Standards Met	CE Certified; RoHS Compliant
User Interface	Indicator LEDs
Charge Current	2 A
Dimensions	120 x 61.6 x 37.4 mm
Input Voltage	100 to 240 V ac
Output Voltage	24 V
Output Voltage @ Charge Current	24 V at 2 A
Weight	0.5 kg
Input Frequency Range	50/60 Hz