



Sample photo

Order symbol: AB 162509
Product nbr: 7083840
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074003560
EI. number:
Finland: 3423490
Denmark: 8212003567
Italy: 7311050
Sweden: 7083840
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		250	160	90	Ingress Protection (EN 60529): IP 66/67
inch:		9.8	6.3	3.5	Impact Resistance (EN 62262): IK 07
Materials:					
Material:		ABS			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
TM 1625		Mounting plate			
TRM 0816		DIN-15 Mounting rail			
TRH 1216		DIN-35 Mounting rail			
TRH 24		DIN-35 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			
					Certificates:
					Gost R

