

tesa® 53327

Basic strength mono filament tape

tesa® 53327 is a basic strength BOPP backed fiberglass reinforced mono filament tape.

tesa® 53327 has a high-tack synthetic rubber adhesive system. It has a good tear resistance and low elongation and is ideally suited for general purpose packaging and bundling applications.

Main Application

- General purpose bundling of heavy transport units
- Reinforcement of boxes and pallets for transportation
- Sealing of heavy cardboard boxes
- Bundling of flexible products such as flooring materials
- Splicing of furniture backboards for folding and transportation

Technical Data

▪ Backing material	glassfibre / BOPP	▪ Adhesion to steel	6 N/cm
▪ Total thickness	95 µm	▪ Elongation at break	4 %
▪ Type of adhesive	synthetic rubber	▪ Tensile strength	175 N/cm

For latest information on this product please visit <http://l.tesa.com/?ip=53327>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.