

Datasheet

## RS Pro Plain Countersunk Stainless Steel Tamper Proof Security Screw, M3 x 12mm

RS Stock No: **262-5651**



### Product Details

RS Pro hexalobular recessed countersunk screw made of A2 grade 18/8 stainless steel, offers corrosion resistance. The screw has metric threading for tight and secure fittings. This tamper proofed security screw measures 12 mm long and has M3 size threads positive grip.

### Features and Benefits

- To DIN 7991
- A2 grade 18/8 stainless steel construction
- Can be used up to 800°C
- Suitable for use in most food, medical, chemical, construction, electronic and domestic applications
- Countersunk head
- Hexalobular recess



**Specifications:**

Drive Type	Torx
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	12 mm
Stainless Steel Type	304 (A2)
Thread Size	M3
Head Diameter	5.8 mm
Head Height	1.65 mm
Specification	DIN 965T