9001KXRJ119

Combination Pushbutton+Pilot Light, Illuminated

Technical Characteristics

Bezel Material	Chromium Plated Metal
Button/Cap Color	Green - Red
Ampere Rating	10A
Approvals	UL Listed File Number E42259 CCN NKCR - CSA Certified File Number LR25490 Class 3211 03 - CE Marked
Button Type	Standard
Catalog Reference Number	9001CT0001
Contact Configuration	1 N.O./1 N.C.
Contact Material	Silver Alloy
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Enclosure Rating	NEMA 4/4X/13; IP65
Head Type	Square
Lens Color	Red
Light Module Supply Voltage	110/120VAC@50/60Hz
Markings	START/ON/STOP
Light Module Type	Transformer
Maximum Voltage Rating	600V
Mounting Type	Panel
Mounting Position	All
Number of Operators	3
Operators	(2) Maintained Pushbuttons (with interlock) - (1) Pilot Light
Operator Type	Illuminated
Terminal Type	Screw Clamp
Size	30mm
Utilization Category	AC15 - DC13
Туре	KX

Shipping and Ordering

Category	21427 - Push Buttons, 30 mm, Square, Type KX
Discount Schedule	CP1
Article Number	785901017448
Package Quantity	1
Weight	0.3 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Υ

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Schneider

Generated: 06/05/2009 10:37:21