

4 way FCC 68 data cable



Part NO: RGW-1564

Product Code: 4 way FCC 68 data cable

Product Description

Application:

For communication and signal control systems.

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

4

Cable Construction


Conductor	Bare Copper
Construction	0.16±0.005x7
Stranded Dia.(±0.01mm)	0.49
Insulation	PE
Thickness	0.21
Insulation Dia.(±0.05mm)	0.95
Insulation Color	1,Black; 2,Red; 3,Green;4, Yellow
Filler	Chalk
Jacket	PVC
Thickness(mm)	0.60
Dia.(±0.15mm)	5.1×2.5
Jacket Color	Grey(RAL7001)

Marking

No Marking

PACKAGING


100M Coil
8Pcs/Box



Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	132
Min.Insulation DC Resistance at 20°C (MΩ *Km)	>500
Rated Temperature(°C)	-20 to +60
Rated Voltage(V)	150

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls(PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	

Label for each coil

Product label

4 way FCC 68 data cable
Grey
100M
RoHS(2002/95/EC) Compliant
WW/YY

RS label

7492516
100M
Made in China


Date: 2011-09-13

Page: 1 / 1