

Datasheet

## RS Pro Magnetic Lock, 1670N

RS Stock No: **739-3239**



### Product Details

RS Pro magnetic lock provides a holding force when energised and releases when de-energised. This electromagnetic lock offers 1670 N dynamic holding force capacity and is suitable for typical applications such as machine mechanisms, door/guard locking and remote hold/release requirements.

### Features and Benefits

- Holding force of 1670 N
- Suitable for typical applications such as machine mechanisms, door/guard locking and remote hold/release requirements
- Provides a holding force when energised and releases when de-energised.



ENGLISH

### Specifications:

AC or DC Operation	AC
Diameter	65 mm
Holding Force	1670 N
Length	111 mm
Supply Voltage	240 V ac
Application	Machine Mechanisms, Door/Guard Locking & Remote Hold/Release Requirements
Current Rating	50 mA
Finish	Bright Nickel Plated with Machined Face
IP Rating	IP54
Power Consumption	10.7 W