



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 7:44 (UTC)

6010

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	50	mm	Bore diameter
D	80	mm	Outside diameter
B	16	mm	Width
r (min.)	1	mm	Chamfer dimension

Basic Load Ratings

Cr	24000	N	Basic dynamic load rating
C0r	16600	N	Basic static load rating

Speeds

Grease	9500	min-1	Grease lubrication
Oil (Oil-bath)	11000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	55	mm	Diameter of shaft abutment
da (max.)	58.5	mm	Diameter of shaft abutment
Da (max.)	75	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	15.6		Factor
----	------	--	--------

Additional information

z	14		Number of Balls
Dw	8.731	mm	Ball Diameter

Mass

Mass approx.	0.261	kg	Mass approx.
--------------	-------	----	--------------

