



Mounting plate H: 1900 mm W: 800 mm

Model	
product brand name	SIVACON S4
product designation	mounting panel
design of the product	Section-high
General technical data	
surface processing	Galvanized
product feature perforated	No
Mechanical Design	
height	1 900 mm
width	800 mm
depth	25 mm
net weight	25 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

other	Environment
Miscellaneous	Environmental Con- firmations
	Environmental Con- firmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ3000-0BA36 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/8PQ3000-0BA36 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ3000-0BA36 CAX-Online-Generator http://www.siemens.com/cax Tender specifications http://www.siemens.com/specifications

last modified:

4/29/2025 

