



E32-ET16WR-2 2M

Fiber optic sensor head, through-beam, square, side-view, 50 mm area detection, R1 flexible fiber, 2 m cable

Specifications

Sensing method	Through-beam
Sensing height	50 mm
Sensing distance	4000 mm
Cable length	2 m
Features	Flexible fiber
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP54
Sensing surface orientation	Side-view
Shape	Square
Material sheath	Polyethylene

Fits to



E3NX-FA41 2M

Fiber amplifier, twin digital display, smart tuning, PNP, single output, 2 m cable



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Optic Sensors Group Catalogue

EN PDF 7.54 MB