

MNX ABS 150/60 HT



Sample photo

Order symbol: ABS 150/60 HT
Product nbr: 6081913
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074023179
El. number:
 Finland 3420631
 Denmark 8212023563
 Italy 7362090
 Sweden 2535851

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions: | L | W | H | Rating: |
|-------------|-----|-----|-----|---|
| mm: | 180 | 130 | 60 | Electrical insulation: Totally insulated |
| inch: | 7.1 | 5.1 | 2.4 | Halogen free (DIN/VDE 0472, Part 815): Yes |

| Materials: | |
|-------------------------------|-------------|
| Material: | ABS |
| Gasket material: | TPE |
| Base colour: | RAL 7035 |
| Cover colour: | Smoked grey |
| Cover screws material: | Polyamide |
| Cover screws colour: | Black |

Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 07

| Temperatures: | |
|--------------------|----------------|
| Short term: | -40 ... 80 °C |
| Continuous: | -40 ... 60 °C |
| Short term: | -40 ... 175 °F |
| Continuous: | -40 ... 140 °F |

Certificates:
 Fimko
 Europe EN 50298: 1998
 Gost R

| Accessories: | |
|--------------|-----------------------------------|
| MIV 150 | Mounting plate (Galvanized steel) |
| MIN 10 | DIN-15 Mounting rail |
| MIN 15 | DIN-15 Mounting rail |
| MIV 10 | DIN-35 Mounting rail |
| MIV 15 | DIN-35 Mounting rail |
| FP A 150/180 | Front plate (Aluminium) |
| HFP 180 | Front plate hinge series (2 pcs) |
| FP 22046 | Wall fastening lug (4 pcs) |

