

TECHNICAL DATA SHEET

SRC03 HYGIENE LACE-UP SHOE

**WASHABLE
MICROFIBRE
UPPER**

**PROTECTIVE STEEL
TOE CAP**

**SELF-CLEANING
ANTI-SLIP SOLE**



DESCRIPTION

Ideal for indoor cleanroom environments such as food preparation, medical and pharmaceutical where there is a risk of slipping on wet or dry tiled surfaces, Blackrock's Hygiene Lace-Up Shoe features a steel toe cap and water resistant microfibre upper that can be machine washed at 40°C. The lightweight, anti-slip PU sole is self-cleaning, anti-static and resistant to oils, acids and fuel oil.

SIZES

Size 3-13 (available
in size 6.5 and 10.5)

STANDARDS

EN20345 S2 SRC

KEY FEATURES

- Machine washable at 40°C
- Steel toe cap with anti-slip, self-cleaning sole
- Energy absorbing heel reduces foot fatigue

FEATURE ICONS



TECHNICAL DATA SHEET

MATERIALS

- Microfibre upper
- PU sole
- Steel toe cap

TYPICAL INDUSTRIES

- Pharmaceutical
- Hygiene & catering

CERTIFICATION/MARKINGS



EN ISO 20345:2011 is an internationally recognised standard which specifies requirements for safety footwear. Any product which references an EN standard must have the relevant certification attributed to the product code found on the product.

The product standard can be found on the tongue label and should match that stated on the certification. The standard is usually a group of numbers and letters, for example S3 WR HRO SRC. These letters and numbers denote the characteristics that make up the footwear you are buying which include properties such as protective toe cap, water-resistant uppers, protective midsole, fuel oil resistance, anti-static, heat resistance and slip resistance.

Users are advised to select the required class of performance based on the risk assessment of the location and/or task as appropriate.

PRODUCT DETAILS

CODE	SIZE	COLOUR	BARCODES	PACKAGING
SRC0303	3	White	5019200181797	Each pair individually boxed Purchase multiple: 1 Outer carton quantity: 10 
SRC0304	4	White	5019200181803	
SRC0305	5	White	5019200181810	
SRC0306	6	White	5019200181827	
SRC03065	6.5	White	5019200196036	
SRC0307	7	White	5019200181834	
SRC0308	8	White	5019200181841	
SRC0309	9	White	5019200181858	
SRC0310	10	White	5019200181865	
SRC03105	10.5	White	5019200196043	
SRC0311	11	White	5019200181872	
SRC0312	12	White	5019200181889	
SRC0313	13	White	5019200181896	