

Single- LED

10-
4H22.1036P

Distribution by
Rs-online



<https://rs-online.eao.com/p/10-4H22.1036P>

Your product:



10-4H22.1036P Single-LED

OPERATING-/INDICATION PART

Illumination colour: Blue

ELECTRICAL CHARACTERISTICS

Operating voltage: 110 V AC/DC

Operation current: 2 mA -30%/+25%

Lumi. Intensity: 4 x 86 mcd

MECHANICAL CHARACTERISTIC

Weight: 0.002 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Single-LED, BA9s, Blue, 110 V AC/DC

Kind of illumination: Multi-LED EN 50155

Hints: A suitable LED remover Part No. 700.006.0, The luminous intensity stated is for when used with DC, Electrical and optical data are measured at 25 °C, The specified 72 and 110 VAC/VDC versions are built with a bridge rectifier, The specified case one LED fails, the other pair of still functioning LED-s is working. The light output then is half in order to indicate the malfunction and shows this way the need for replacement, Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

Wiring diagrams:



Dimension drawings:

