

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Article No.	115100
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	White/Transparent
Finish	Matt
Order Reference	M71-31-427
Printable Area - Height (mm)	12.70
Printable Area - Width (mm)	25.40
Printer Compatibility	BMP71
Size - Height (mm)	38.10
Size - Width (mm)	25.40
Additional Information	Self-Laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	250 Label(s) / Box
Vertical Repeat (mm)	28.58
Wire Gauge	10-4
Approval/Compliance	UL Recognised
Ribbon Series	M71-R4300
Application	Voice & Data Communication; Wire & Cable Marking
Industry	Aerospace;Data & Telecommunications;Defence;Electrical;Mass Transit
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL Approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	24
Max. Lines of	5

Text	
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	8.10
Min. Service Temp. °C	-80
Min. Wire/Cable Diameter (mm)	4.00
Shape	Rectangle
Surface	For smooth & textured/rough surfaces
Voice/Data Application	4 Pair UTP; CAT 5; CAT 5E; CAT 6; RG-59 Coax; RG-6 Coax; Silver Satin