

Typical places of use:
Foundries, welding and fabricating

Special Hazard

HM2006WSI

Ankle foundry boot

Standard	ENISO 20349:2017
Category	S3 HI HRO SRC Fe
Code	HM2006WSI
Product Type	Ankle boot
Colours	Black
Size Range	5 - 13 UK
Weight	850gr
Upper	2.2 - 2.7mm flame retardant, hydrophobic, waterproof and breathable full grain cow hide leather
Inner Lining	Moisture wicking textile to vamp
Soling Technology	Flame resistant dual density rubber soling system with antistatic properties along with excellent shock absorption, cushion comfort and heat resistance to 300°C.
Comfort Features	Removable, washable felt footbed
Additional Features	Quick release velcro fastening

Steel toe cap ✓ Steel midsole ✓ Heat resistant to 300°C ✓
Slip resistant ✓ Antistatic ✓ Oil resistant ✓

Quick release velcro



DDR technology



Non clogging sole pattern

High slip resistant sole unit



DDR

SRC