



182.72.104.66PASEStehlager-Gehäuseeinheiten

Plummer block housing units

PASE50-XL-N (Series PASE)

cast iron housing, radial insert ball bearing with eccentric
locking collar, P seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	50 mm
L	200 mm
H ₂	115 mm
A	54 mm
A ₁	34 mm
B ₁	43,8 mm
d ₃ max	69 mm
H	57,2 mm
H ₁	21,5 mm
J	158 mm
N	18 mm
N ₁	23 mm
Q	Rp1/8
S ₁	32,8 mm
m	2,59 kg Mass
C _r	37500 N Basic dynamic load rating, radial
C _{0r}	23200 N Basic static load rating, radial
	ASE10 Designation of housing
	GRAE50-XL-NPP-B Designation of bearing
	KASK10 Bearing end cap, closed design. To be ordered separately.
	Slot for bearing end cap

