



Hedge Trimmer LXT®

DUH606

18V • 600 mm • 30T • 4,000 min⁻¹

Model DUH606 is a 600mm (23-5/8") cordless hedge trimmers powered by 18V LXT® Li-Ion battery.

Lightweight design. Constant speed control. Anti-restart function. Brushless Motor.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Strokes per Minute (SPM)	4000 min ⁻¹
Length Of Blade	600 mm
Max blade opening	20 mm
Tooth Spacing	30 mm
Continuous Use 18V / 6.0 Ah Battery	70 min
Sound Power Level (L _{WA})	90 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Compact and lightweight design
- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing