

Blower XGT®

UB002G

Model UB002G is a blower powered by a 40Vmax XGT® Li-ion battery.

Compact and lightweight, easy to manoeuvre. The air volume has been enhanced by changing the shape to optimise the airflow path. Features and benefits: 3 stage air volume settings by dial with variable speed control by trigger, Vacuum function.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 18000 min ⁻¹
Max. Air Velocity	99 m/s
Blowing force	3,0 - 3,2 N
Air volume	0 - 3,6 m ³ /min
Max. sealed suction	54 mbar
Continuous use XGT® 40Vmax / 2.5 Ah	120 / 60 / 20 min
Sound Power Level (L _{WA})	91 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Product net weight	1,2 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,0 - 3,5 kg

User benefits

- Compact and lightweight for single handed operation
- 3 air volume setting (high/medium/low)
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Compatible with various nozzle accessories for increased versatility

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing