

Handling module HSW-10-AP

Part number: 540222

FESTO



 General operating condition

Data sheet

Feature	Value
Working stroke	9 mm ... 15 mm
Size	10
Max. linear stroke with 90° swivel angle	90/90 mm
Z stroke	80 mm ... 100 mm
Cushioning	Shock absorber at both ends Soft characteristic curve
Mounting position	optional
Design	Force pilot operated motion sequence
Position detection	Via proximity switch
Operating pressure	4 bar ... 8 bar
Min. cycle time	0.6 s
Repetition accuracy end positions	+/-0.02 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. moment Mx	0.6 Nm
Max. moment My	0.6 Nm
Max. moment Mz	0.6 Nm
Max. effective load	0.5 kg
Max. process force in Y direction	30 N
Theoretical force at 0.6 MPa (6 bar, 87 psi)	30 N
Product weight	1250 g
Type of mounting	Via through-hole and centring sleeve
Pneumatic connection	M3
Material stops	High-alloy steel
Material spring pressure piece	High-alloy steel
Material base plate	Wrought aluminium alloy Anodised
Material retaining bracket	Anodised
Material cross-guide	Tempered steel
Material swivel lever	Case-hardened steel Burnished
Material slotted guide plate	Case-hardened steel Burnished

Feature	Value
Material sensor rail	Wrought aluminium alloy Anodised
Material bar	Wrought aluminium alloy Anodised
Material setting screw	High-alloy steel