

FEATURES

- 2 Part Gland
- High mechanical strength
- -100°C to +300°C

RS PRO Nickel Plated Brass Male Fixed Flexible Conduit Gland 32mm

RS Stock No.: 2149563



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

General Specifications

Material	Nickel Plated Brass
Colour	Self Colour
Conduit Type	Flexible
Qty per pack	2
Maximum Operating Temperature	+300°C
Minimum Operating Temperature	-100°C
Nominal Size	32mm
Thread Size	M32

Compatible Conduits

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
2149594	RS PRO	Flexible Conduit	Galvanised Steel	IP40	-100°C to +300°C
2149585	RS PRO	Flexible Conduit	PVC Coated Galvanised Steel	IP54	-15°C to +70°C