

E.306A - ELECTRONIC TORQUE WRENCHES WITH RATCHET | E.306A135J



Norm :

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description

- Accuracy: $\pm 2\%$ between 20% and 100% wrench capacity.
- Measuring mode: peak or follower.
- Measuring unit: N.m, lbf.ft, lbf.in and kg.cm.
- Bits: 9 x 12 and 14 x 18 mm.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Presetting possible of 9 torque and/or angle values.
- Memory 250 values with PC USB link.
- Supplied in plastic case with foam interior.

Information

L [mm]	415
[kg]	1,697