

Main

Range of product	KNX
Product or component type	Heating actuator
Operating mode	Manual KNX bus system
Bus type	KNX
Rated output	0.5 A - 5 x for output continuous 0 to 100 % 0.5 A for output switching on/off
Rated input	Signal voltage (SELV): 2 x binary

Complementary

Total number of 18 mm modules	4
Wiring device mounting	DIN rail
[Ue] rated operational voltage	207...253 V
Load type	Valve: 230 V AC Valve: 24 V AC

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins