

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **Bore Size of 12.02 mm:** Fits standard shafts for versatile use.
- **Outside Diameter of 18.04 mm:** Compatible with a wide range of housings.

RS PRO 12.02 mm Flanged Plain Bearing

RS Stock No: 528-061



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for smooth and efficient operation in various industrial applications. Made from high-quality sintered bronze, it offers excellent durability and reliability. Ideal for use in machinery where low friction and high load capacity are essential.

General Specifications

Bore Size	12.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	18.04 mm
Width	12 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

