



D25481K

40mm SDS-Max Combination Hammer

Selling Proposition

- Ideal for drilling anchor fixing and through holes in concrete and masonry from 12 to 40 mm in diameter. Core drilling up to 100 mm
- Ergonomic, compact and slim line design maximises control and offers easy access to confined spaces
- Rotation stop mode for chiselling and impact stop mode for rotary only drilling with dry diamond cores
- Perform & Protect: low vibration at 9.4m/s², minimising user fatigue

Standard Equipment

- Multi-position side handle
- Heavy duty carrying case

Warranty Specifications

 DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Tool Holder	SDS-Max
Battery chemistry	
Battery Voltage	
Battery Capacity	
Power Input	1050 Watts
Power Output	
Impact energy (EPTA 05/2009)	6.1 J
Load Speed	540 rpm