

## Peltor G2000C

Cool design and highest protection! That's the easiest way to summarise the Peltor G2000. The helmet goes well beyond the requirements for formal testing and is comfortable with its low back and relatively low profile.

It was designed to accommodate additional equipment, such as a lamp or lamp holder (Peltor GLF).

The **highest protection** class according to EN 397, with the following additional approvals:

- G2000\*: low temperature,  $-30^{\circ}\text{C}$ , lateral deformation, LD, and molten metal, MM
- G2001\* (not ventilated): low temperature,  $-30^{\circ}\text{C}$ , lateral deformation, LD, molten metal, MM, and electrical insulation, 440Vac
- G2001\* 1000V (not ventilated): in addition, the G2001 is approved according to EN50365, a 1000-volt helmet

**Material:** UV-stabilised ABS

**Colours:** Grey, yellow, white, orange, red, blue and green.

**Weight:** 340 g.

**Size:** 54-62 cm.

