



General characteristics

Colour	Yellow
Type of positions	Mushroom head pushbutton
Material	Polycarbonate
IEC degree of protection	IP66, IP67, IP69K


Mechanical features

Tightening torque for terminals max	Nm	1
-------------------------------------	----	---

Ambient conditions

Temperature	Operating temperature	min	°C	-25
		max	°C	+70
Storage temperature	Storage temperature	min	°C	-40
		max	°C	+85

Dimensions



Certifications and compliance

Certificates

cULus

ETIM classification

ETIM 8.0

EC000225 -
Control circuit
devices
combination in
enclosure