

## Industrial Labeling ~ K3000-PC

- [K3000-PC Features](#)
- [K3000-PC Printing Specs](#)
- [K3000-PC Media Specs](#)
- [K3000-PC Physical Specs](#)
- [K3000-PC Electrical Specs](#)
- [K3000-PC Environmental Specs](#)
- [K3000-PC Limited Warranty](#)
- [Getting Started with the K3000-PC](#)
- [K3000-PC Accessories](#)
- [K3000-PC Cartridge Supplies](#)



### **K3000-PC Series Features:**

- Supply is easy loading
- Print graphics, logos, bar codes, and data records
- Connects to your personal computer
- Compatible with Win95/98/2000 and NT 4.0
- Comes with Kroy Label Designer Software (KLDS) and Windows drivers
- Uses continuous and die cut media
- Supports baud rates of up to 115,200 bps
- Small footprint

### **K3000-PC Series Printing Specifications:**

- Thermal transfer and direct thermal printing
- Print speeds vary by content up to 2" per second

- 300 dots per inch (12 dots per mm)
- Maximum print width: .97" (24.7mm)
- Maximum label width: 1" (25.4mm)
- Maximum label length: 20" (508mm)

### **K3000-PC Series Media Specifications:**

- Tape supply widths: .5", .8", 1"
- Tape supply length: 40 feet (12.2m)
- Shrink Tube supply length: 110" (2.8m)
- Media type: general-purpose (laminated and non-laminated thermal-transfer supply), industrial (UV and chemical resistant supply), die-cut labels (synthetic and polyester), polyolefin shrink tubing, reloadable direct-thermal tape supply, direct-thermal tape supply and tamper-evident supply.
- 10 tape supply colors and 5 ribbon colors
- All supplies are housed in a self-contained cartridge for rapid supply change

### **K3000-PC Series Physical Specifications:**

- Printer module: 6.0" L x 3.75" W x 4" H

### **K3000-PC Series Electrical Specifications:**

- Available with AC adapter.
- AC adapter version: Output: 14VDC, 1.6A - UL Listed, CSA Certified, TUV "GS" Approval, CE Recognized
- Meets VDE-B and FCC Part 15 class B RFI limits
- 9600-115,200 baud, no parity, 8 bits, XON-XOFF protocol

### **K3000-PC Series Environmental Specifications:**

- Operating temperature: 45 F to 105 F (7 C to 40 C)
- Supply cartridge storage temperature: - 60 F to 105 F (15 C to 40 C) shelf life is reduced at higher temperatures - damage may occur at temperatures as high as 120 F (50 C)
- Operating /storage humidity limit: 90% RH non-condensing

**K3000-PC Series Limited Warranty:**

- 1 year parts and labor
- 90 day printhead and software

**Getting Started with the K3000-PC Series Labeling System**

<b>Part Number</b>	<b>Description</b>		
2554400	K3000-PC Label Printer With 120V AC Adapter Serial Cable KLDS Software Drivers		

**K3000-PC Accessories**

<b>Part Number</b>	<b>Description</b>		
2556600	AC Adapter 120v Fits K3000-PC		

**K3000-PC Cartridge Supplies:**

- [.375 Labeling Supplies](#)
  - [.50" Labeling Supplies](#)
  - [.80" Labeling Supplies](#)
  - [1.0" Labeling Supplies](#)
  - [1.0" Cast Vinyl Supplies](#)
  - [Self Laminating Wire Wraps](#)
  - [Shrink Tube](#)
  - [Die Cut Polyester Labeling Supplies](#)
  - [Tamper Evident Labeling Supplies](#)
  - [Photo Clip Cartridge Supplies](#)
  - [Illuminated Directory Supplies](#)
-