

Eaton 12OLGMA160

Catalog Number: 12OLGMA160

Oil fuse-link, medium voltage, 160 A, AC 12 kV, 359 x 63.5 mm, back-up, BS, IEC, ESI, with striker



General specifications

Product Name	Catalog Number
Eaton Bussmann series medium voltage oil fuse	12OLGMA160
	EAN 5027590432948
Product Length/Depth	Product Height
359 mm	65 mm
Product Width	Product Weight
63.5 mm	2600 g
Compliances	Certifications
BS 2692-1 ESI 12-8	IEC60282-1 KEMA

Product specifications

Type

fuse

Application

protection of primary side transformer, and oil-filled fuse switch combination unit

Amperage Rating

160 A

Fuse indicator

with striker

Fuse size

63.5 x 359 mm

Breaking capacity

40 kA

Installation technique

Oil

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

60 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Fuse diameter

63.5 mm

Resources

Technical service bulletins

[Datasheet - 12OLGMA160](#)

Joule integral (I²T) - max operating

1.7 x 10⁵

Joule integral (I²T) - min pre-arcing

1 x 10⁴

Resistance

79

Class

Class back-up

Construction type

F02/BS 2692

Fuse shape

Cylindrical

Interrupt rating

40 kAIC

Construction size

63.5 x 359 mm

Voltage rating

12 kV

Fuse type

OLGM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia