




(0.80 mm) .0315"



## M BODY GROUND PLANE SOCKET

#### **SPECIFICATIONS**

For complete specifications and recommended PCB layouts see www.samtec.com?QRF8

Insulator Material: Black LCI

Contact Material: BeCu.

Ground Plane Material:

Phosphor Bronze

Phosphior Biolize Plating: Au or Sn over 50 μ" (1.27 μm) Ni Current Rating: Contact:

2.2 A per pin (2 pins powered) Ground Plane:

8.5 A per ground plane (1 ground plane powered) Operating Temp Range:

-55 °C to +125 °C Voltage Rating: RoHS Compliant:

**PROCESSING** 

Lead-Free Solderable:

SMT Lead Coplanarity: (0.10 mm) .004" max (018-026) (0.15 mm) .006" max (036-078) (.004" stencil solution may be available; contact IPG@samtec.com)

#### **RECOGNITIONS**

For complete scope of recognitions see www.samtec.com/quality



### **PROTOCOLS**

• 100 GbE

MATED HEIGHT*			
QRF8 LEAD STYLE	QRM8 LEAD STYLE		
	-02.0	-05.0	-07.0
-05.0	(7.00) .276	(10.00) .394	(12.00) .472
-07.0	(9.00) .354	(12.00) .472	(14.00) .551

\*Processing conditions will affect mated height. See SO Series for board space tolerances

#### Notes: Patented

Some lengths, styles and options are non-standard, non-returnable.



Cable Mates:




QRF8

LEAD STYLE

-05.0

-07.0



· Other platings

**PLATING** 

**OPTION** 

## ALSO AVAILABLE (MOQ Required)

Contact Samtec.





Compatible with UMPT/UMPS for flexible two-piece power/signal solutions

# -026, -052, -078(52 total pins per bank = -D)

QRM8-DP/QRF8-DP @ 10 mm Mated Stack Height

Rating based on Samtec reference channel.

For full SI performance data visit Samtec.com

or contact SIG@samtec.com

PINS PER ROW

NO. OF PAIRS

-018, -036, -054 (18 pairs per bank = -D-DP)

Α

(5.01) .197

(7.01) .276

-05.0= 5 mm Body Height -07.0 = 7 mm Body Height

STYLE

= 10 µ" (0.25 µm) Gold on contact, Matte Tin on tail

-D = Single-Ended -D-DP = Differential Pair

**TYPE** 

## -GP


= Guide Post (Requires -GP on mating connector)

**OTHER** 

OPTION

(5.00 mm) .197" DIA Polyimide Film Pick & Place Pad

-TR = Tape & Reel (-018, -026, -036, -052 only)



No. of Banks x (24.80) .976 + (5.25) .206 

-GP OPTION

Due to technical progress, all designs, specifications and components are subject to change without notice

# **RUGGEDIZED**

- Edge Rate® contacts
- · Increased contact
- 10 year MFG
- · Guide post option