

Main

Product or component type	Communication card
Range compatibility	Altivar 61 Altivar 71 Altivar 61Q Altivar 71Q
Communication port protocol	DeviceNet
Connector type	1 screw connector 5 contacts at intervals of 5.08
Transmission rate	125 kbps 250 kbps 500 kbps

Complementary

Number of addresses	1...63
Exchange mode	Inputs : polled, change of state, cyclic Outputs : polled
Communication service	Allen-Bradley drive profile CiA 402 profile : "Device profile Drives and Motion Control" CIP AC Drive (02) profile Communication monitoring can be inhibited, adjustable I/O profile
Display type	1 dual colour LED for MNS (status) Graphic display terminal for control word received Graphic display terminal for reference received
Product weight	0.3 kg

Environment

RoHS EUR status	Compliant
RoHS EUR conformity date	1030