

Part Number:0050375053

Status:Active

Overview:Mini-SPOX Wire-to-Board Connector System

Description:2.50mm Pitch, Mini-SPOX Receptacle Crimp Housing, Single Row, Friction Lock, 5 Circuits, Natural

Documents:

2D Drawing DXF (PDF)	产品规格 52641001-PS-000 (PDF)
2D Drawing (DXF)	产品规格 PS-5264-001-001 (PDF)
3D Model (PDF)	包装规格 SPK-5264-001-001 (PDF)
3D模型	RoHS 证书
图纸 (PDF)	

Agency Certification

一般	
应用	Signal, 线对板
概述	Mini-SPOX Wire-to-Board Connector System
产品名称	Mini-SPOX
UPC	800753725249
物理	
电路数(最多的)	5
颜色-树脂	自然色
阻燃性	94V-0
部件属性	插座
Glow-Wire Capable	否
锁定插接部位	Yes
材料-树脂	尼龙
Net Weight	277.700/mg
行数	1
包装形式	袋
面板安装式	否
间距-接合界面	2.50mm
有极性的插配件	Yes
可堆叠的	否
运行温度范围	-40° to +105° C
材料信息	
Engineering Number	5264-05
参考: 图纸编号	
包装规格	SPK-5264-001-001
产品规格	52641001-PS-000, PS-5264-001-001
销售用图纸	52640001-SD-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -	
D (2022) 4187-DC (10	
June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit	
Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5264 Series

Mates With

Mini-SPOX Vertical Header 5267 . Mini-SPOX Right-Angle Header 5268

Use With

Mini-SPOX Receptacle Terminal 5263