Features

- Integrated TAGO (Tag + Hasp) lockout device.
- Anodised aluminium body for strength and corrosion resistance.
- High-visibility red finish for quick identification.
- Supports up to 6 padlocks for group lockout applications.
- Lightweight yet durable for industrial use.
- Ideal for switchgear, valves, breakers, and general isolation points.

RS PRO TAGO Lockout Hasp Electroplated - Red 6 Hole

RS Stock No.: 0802199



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Integrated Tag + Hasp Design (TAGO)*** *- Combines the functionality of a standard lockout hasp and safety tag into one device, improving efficiency and simplifying lockout procedures.*
- ***High-Visibility Red Finish*** *- Bright red colour ensures clear visibility in industrial environments, helping identify active lockout points instantly.*
- ***Durable Anodised Aluminium Construction*** *- Manufactured from* ***anodised aluminium****, providing lightweight strength, corrosion resistance, and long-term reliability.*
- ***6-Person Group Lockout Capacity*** *- Accommodates up to* ***6 personal padlocks****, enabling safe multi-worker lockout applications.*
- ***Efficient & Space-Saving Design*** *- Eliminates the need for separate tagging devices, reducing clutter and streamlining maintenance procedures.*

General Specifications

Type	Lockout Hasp
Material	Aluminium
Colour	Red
Padlock holes	6
Package	PE-LD

Mechanical Specifications

Dia (Jaw Size)	27mm
Body - Width	77mm
Body - Height	188mm
Accepts Shackle Dia	7mm
Weight	126 Grams

Operation Environment Specifications

Withstand temperature	-30°C to 175°C


DANGER
DO
NOT
OPERATE