

LE 9-11 125

Universal 900 watt angle grinder, 125 mm

Order no. 436291

GTIN 4030293189133



- + Microprocessor electronics: with tachogenerator constant speed control, speed control, soft start, restart protection after power failure, overload protection
- + Variable speed adjustment (6 settings)
- + Anti-Kickback - this shuts down the motor on the disc being blocked
- + Highly efficient and resilient motor for more power output
- + Longer service life thanks to optimised cooling and revised carbon geometry
- + Extensive dust protection for motor and gears
- + Extremely light and handy
- + Compact, narrow and ergonomic shape
- + Tool-free adjustment of safety guard
- + Lockable slide switch
- + Spindle lock
- + This universal angle grinder is suited for steel/metal surface finishing, for work on the site/renovation as well as for vehicle bodywork and construction firms
- + Side handgrip



Technical data

Power consumption	900 W
Power output	600 W
Voltage	230 V
Frequency	50/60 Hz
Max. disc diameter	125 mm
No-load speed	6000 - 11500 rpm
Angle grinder material	M14
Cable length	4.0 m
Dimensions WxLxH	300 x 75 x 105 mm
Weight	2.0 kg

Standard equipment

- 1 Sanding guard (436860)
- 1 Clamping flange (335282)
- 1 Clamping nut M 14 (100080)
- 1 Face pin spanner (100110)
- 1 Handle (450774)