

Main

Range	Actassi
Product or component type	Singlemode fibre optic adapter
Colour	Blue
Type of packing	Bag
Quantity per set	1

Complementary

Minimum number of matings	200 cycles
Optic fiber diameter	9/125 µm
Fibre performance	OS1 OS2
Connector type	LC duplex sq
Material	Zirconia: ferrule
Fixing mode	By clips
Width	13 mm
Height	15.3 mm
Length	25 mm
Targeted region	Asia Pacific. Europe

Environment

Ambient air temperature for operation	-25...85 °C
Ambient air temperature for storage	-25...85 °C
Standards	LC adapter: TIA/EIA-604-10 A LC adapter: IEC 61754-20 Ed.2 ISO/IEC 11801:2011 Ed.2.2

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations