

# XID200

## Features:

- Pressure developing, centrifugal fans suitable for extract or intake.
- Comprehensive 6 model range.
- Compact and robust zintec steel construction.
- Can be mounted to run in any position.
- Designed for ease of installation and low maintenance.
- Totally enclosed, lubricated for life motors.
- Motors protected to IP44.
- Speed controller available for all models.
- Standard thermal overheat protection.
- 3 year guarantee (UK - ONLY).
- Export Customers see your Local Distributor.




## Performance:

Standard models are single phase 240V 50Hz. The electrical connection terminal box, protected to IP54, also contains the motor capacitor. A 20mm diameter entry and grommet is provided. All models can be operated direct by a remote switch (not provided) or a speed controller model XIC1 available as an ancillary.

Air Flow at FID (m <sup>3</sup> /sec):	0.305
Sound Pressure (dB(A)):	51
RPM:	2500
Weight (kg):	5
Max Ambient Temperature:	40
Frequency (Hz):	50
Ducting Dia. (mm):	200 (7.87 inches)
Voltage:	240V
Mounting:	Ducted
Usage:	Pub, Bar, Cafe, Restaurant, Office, Public Toilet, Washroom

# XID200

## Performance



XID RANGE