


## DIMMABLE DOWLIGHT PRO Ø220

LD4DWL2452BD

24,0 W - 2400lm - 3000K



| DIMENSIONS | A  | B   | C   |
|------------|----|-----|-----|
| 1          | 69 | --- | 220 |



| GENERAL INFORMATIONS        |                            |
|-----------------------------|----------------------------|
| Code                        | LD4DWL2452BD               |
| Ean                         | 8031453019440              |
| Family                      | DIMMABLE DOWLIGHT PRO Ø220 |
| Technology                  | LED                        |
| Body material               | Aluminum                   |
| Diffuser / lens material    | PC                         |
| Operating temperature (° C) | -20 - +40                  |

| PACKAGING |     |
|-----------|-----|
| Packaging | BOX |
| Pack      | 10  |

| LIGHTING DATA              |       |
|----------------------------|-------|
| Kelvin (°)                 | 3000  |
| Lumen                      | 2400  |
| Candela (cd)               | 1000  |
| Beam (°)                   | 100   |
| Luminous efficacy (lm / W) | 100,0 |
| Color rendering (CRI)      | >80   |

| TECHNICAL FEATURES           |           |
|------------------------------|-----------|
| Power (W)                    | 24,0      |
| Supply voltage (V) / Max (V) | 220 / 240 |
| Power frequency (Hz)         | 50/60     |
| Hole diameter (mm)           | 205       |
| Power factor                 | >0,9      |
| Dimmer compatibility         | SI        |

## **DIMMABLE DOWLIGHT PRO Ø220**

LD4DWL2452BD

24,0W - 2400lm - 3000K

- Die-cast aluminium body for greater heat dissipation
- External dimmable flicker-free driver
- Dimmable (TRIAC)
- IP44 front protection rating (IP20 rear and driver)