

- Universal input voltage
- Compact and light weight
- Efficiency level V
- Mains plug included
- Exchangeable AC plugs
- Exchangeable DC plugs
- Universal inngangsspenning
- Kompakt enhet, lett vekt
- Effektivitetsnivå V
- Nettplugg inkludert
- Utskiftbare AC plugger
- Utskiftbare DC plugger



Technical specifications

Tekniske data

Input voltage:	Inngangsspenning:	90-264 VAC, 50/60 Hz
Line frequency:	Frekvensområde:	47-63 Hz
Max. output power:	Maks. utgangseffekt:	25 W
Load regulation:	Lastregulering:	4-5 %
Mains regulation:	Linjeregulering:	< 1 %
Ripple:	Rippel:	2% max
Efficiency, approx.:	Virkningsgrad, ca.:	>82,4% (avg. of 25,50,75 and 100% load)
Standby power:	Tomgangseffekt:	≤ 0,3 W
Hold up time:	Hold up time:	12 ms (min)
Temperature range	Temperaturområde	
• Operating:	• Drift:	-20°C - +40°C
• With derating:	• Med derating:	+70°C
• Storage:	• Lagring:	-40°C - +85°C
Derating:	Derating:	0,42W/°C over 40°C
Insulation class:	Isolasjonsklasse:	II
Insulation voltage	Isolasjonsspenning	
• Primary - secondary:	• Primær - sekundær:	4242VDC (min)
Safety:	Sikkerhet:	EN 60950
EMC standards	EMC standarder	
• Emission:	• Emisjon:	EN 61000-6-3
• Immunity:	• Immunitet:	EN 61000-6-1
Reliability (MIL-HDBK-217F):	Pålitelighet (MIL-HDBK-217F):	MTBF > 100.000 hrs at 25°C
Output terminal:	Utgangsterminal:	1,2 m cable with exchangeable output plug 1,2 m sekundærledning med utskiftbar plugg
Dimensions (LxWxH):	Ytre mål (LxBxH):	75 x 43 x 40 mm
Weight:	Vekt:	125 g

Voltage versions - Spenningsversjoner

Output (V) Utgang (V)	Max. current (A) Maks. strøm (A)	Max. output power (W) Maks. utgangseffekt (W)
12	2,08	25
24	1,04	25

Safety approvals - Godkjenninger

