FloorPro Deep Cleaner, acidic RM 751

Acidic deep cleaner for manual and mechanical sanitary and building cleaning. Effectively removes limescale, calcareous deposits, rust, milkstone, urine scale and cement film.

pH value 1
in concentrate



Made in Germany

NTA-free

Properties

- Powerful, acidic deep cleaner for all acid-resistant hard floors
- Removes stubborn limescale, rust, grease, protein, beer and milkstone soiling
- Effectively removes cement film
- Very low foaming
- With integrated corrosion protection
- Quick oil and water separation in the oil separator (easily separable = asf)
- NTA-free

Application areas

Building Industry	Post-construction cleaning
Building cleaning	Floor cleaning, Post-construction cleaning
Industry	Floor cleaning
Municipal	Floor cleaning

Usage options

- Scrubber driers
- Manual

Technical data

Container sizes	Packaging unit	Part number
2.5 l	4 Piece(s)	6.295-586.0
10 l	1 Piece(s)	6.295-129.0

FloorPro Deep Cleaner, acidic RM 751, 0.011-136.0, 2026-05-08

We would be happy to advise you:

Application

Scrubber-driers – deep cleaning
- Use appropriate brush/roller/pad and squeegee for scrubber drier as required.
- Combine the product with the appropriate dosage and fresh water.
- Soak any cement joints thoroughly.
- Wet surface evenly with product (using brush/roller/pad as required).
- Allow to soak.
- Contact time 1-5 minutes, depending on the degree of soiling.
- Vacuum the dirty water from the surface in overlapping sections.
- Rinse with plenty of clear water and soak in water until all dirt and cleaning agent residues have been removed.

Scrubber driers – maintenance cleaning
- Remove coarse dirt by sweeping.
- Combine the product with the appropriate dosage and fresh water.
- On DOSE machines, set the dosing only on the device.
- Clean and vacuum the surface with a scrubber dryer using the 1-step method.

Manual
- Remove coarse dirt by sweeping.
- Combine the product with the appropriate dosage and fresh water.
- Clean surface manually.

Instructions for use

- In the food sector, rinse thoroughly with drinking water.
- Test on an inconspicuous part for material compatibility.
- Do not apply to polished marble or acid-sensitive materials.
- Do not let the cleaning solution dry out.
- Store away from frost.

Warnings and safety recommendations according to EC Directives

- Danger
- H290 May be corrosive to metals
- H314 Causes severe skin burns and eye damage
- P280 Wear protective gloves/protective clothing/eye protection/face protection.
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
- P405 Store locked up.
- P501a Dispose of contents/container in accordance with local/regional/national/international regulations.

Further information

- Material Safety Data Sheet (MSDS)

Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1000 ml	Deep cleaning	5 – 25 %	strong	370 m²
1000 ml	Maintenance cleaning	1 – 5 %	medium	2440 m²
1000 ml	Manual	0.5 – 1 %	mild	

We would be happy to advise you: