

Product data sheet

Specifications



Repacked, Switch, Mureva Styl, complete product, 1-pole 2-way, electromechanical, 10AX, IP55, white

MUR39021W



This repacked option saves 0.586 over the standard condition

Main

Range	Mureva Styl
Range of product	Mureva Styl
Product or component type	Switch
Colour tint	White (RAL 9003)

Complementary

Device presentation	Complete product
Device mounting	Surface
Rated current	10 AX
surface treatment	Untreated
Surface finish	Matt
Switch function	1-pole 2-way
[Ue] rated operational voltage	250 V
Technology type	Electromechanical
fixing mode	By screws
Load type	Load for energy saving lamps with ballast: 100 W
[Ue] rated operational voltage	250 V AC
Number of rocker	1
Actuator	Rocker
Cable entry	Easy valve access diameter: 6...20 mm
Clamping connection capacity	1.5...2.5 mm² for rigid cable(s) 1.5...2.5 mm² for stranded cable(s) 1.5...2.5 mm² for flexible cable(s)
Connections - terminals	Screw terminals
Width	76 mm
Height	76 mm
Depth	64 mm
Projecting depth	64 mm
Material	SEBS ABS (acrylonitrile butadiene-styrene) Brass
Condition of use	Indoor/outdoor

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Wire stripping length	13 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	CE EAC AENOR NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	7.500 cm
Package 1 Length	7.500 cm
Package 1 Weight	128.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.468 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.6 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

C6de3800-7220-4403-a6a2-26e1f05e3f4b

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins