
KEMET Part Number: SSHB10HS-05177

(UALSB1S0517700)



KEMET, SSHB10HS, AC Line Filters, Dual Mode, 0.0177 H



General Information		
Series:	SSHB10HS	
Style:	Through-Hole	
RoHS:	Yes	
Notes:	Marking: 05 Lot No.	
Miscellaneous:	Temperature Rise Maximum: 50 K	

Specifications	
Voltage AC:	250 VAC
Inductance:	17.7 mH (10 kHz)
Current:	500 mA
Temperature Range:	-25/+130°C
DC Resistance:	1.55 Ohms

Dimensions		
L	22mm MAX	
т	17mm MAX	
Н	15.5mm MAX	
LL	3.5mm +/-0.5mm	
S	13mm +/-0.5mm	

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	300
Weight:	10 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

